

Han CGM-M M12x1,5 D. 3-6,5mm



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 00 000 5026 |
| Specification | Han CGM-M M12x1,5 D. 3-6,5mm |
| HARTING eCatalogue | https://b2b.harting.com/19000005026 |

Identification

| | |
|--------------------------|------------------------|
| Category | Accessories |
| Series of hoods/housings | Han [®] CGM-M |
| Type of accessory | Cable gland |

Technical characteristics

| | |
|--|--|
| Wrench size | 14 |
| Limiting temperature | -40 ... +100 °C |
| Degree of protection acc. to IEC 60529 | IP68 IP69 / IPX9K acc. to ISO 20653 |
| Size | M12 |
| Clamping range | 3 ... 6.5 mm |
| Width across corners | 15.5 mm |

Material properties

| | |
|-----------------------------|--|
| Material (seal) | NBR |
| Material (cable glands) | Brass |
| Material (clamping ring) | Polyamide (PA) |
| Surface (accessories) | Nickel plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |



Pushing Performance

Material properties

| | |
|----------------------------|------|
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 0.01 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27144432 Screwed cable gland (electr.) |