

## Han CGM-M M16x1,5 D. 5-10mm



Part number	19 00 000 5030
Specification	Han CGM-M M16x1,5 D. 5-10mm
HARTING eCatalogue	https://b2b.harting.com/19000005030

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-M
Type of accessory	Cable gland

## Technical characteristics

Wrench size	20
Limiting temperature	-40 +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M16
Clamping range	5 10 mm
Width across corners	22.2 mm

## Material properties

Material (seal)	NBR
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No

Page 1 / 2 | Creation date 2021-02-25 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties	
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
Specifications and approvals	
Approvals	DNV GL
Commercial data	
Packaging size	10
Net weight	0.023 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)