

## Han-Eco 10B Outd-HSM1-with DL-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 210 0230
Specification	Han-Eco 10B Outd-HSM1-with DL-M20
HARTING eCatalogue	<a href="https://b2b.harting.com/19432100230">https://b2b.harting.com/19432100230</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco <sup>®</sup> B
Type of hood/housing	Surface mounted housing

### Version

Locking type	Double locking lever
Size	10 B
Version	Side entry
Cable entry	1x M20

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)



Pushing Performance

## Material properties

Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
CE	Yes

## Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors