

## RJI RJ45 PN plug Cat5, 4p IDC straight



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1120
Specification	RJI RJ45 PN plug Cat5, 4p IDC straight
HARTING eCatalogue	<a href="https://b2b.harting.com/09451511120">https://b2b.harting.com/09451511120</a>

### Identification

Category	Connectors
Series	HARTING RJ Industrial®
Element	Cable connector
Specification	Straight

### Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4

### Technical characteristics

Conductor cross-section	0.1 ... 0.32 mm <sup>2</sup>
Conductor cross-section	AWG 27 ... AWG 22
Wire outer diameter	1.6 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm



Pushing Performance

## Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 45545-2 R26: HL1, HL2, HL3
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

## Commercial data

Packaging size	10
Net weight	24.5 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)