

Han 1A-strain relief



Image is for illustration purposes only. Please refer to product description.

Part number	09 10 000 5300
Specification	Han 1A-strain relief
HARTING eCatalogue	https://b2b.harting.com/09100005300

Identification

Category	Accessories
Series	Han [®] 1A
Type of accessory	Strain relief

Version

Details	A Han [®] 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector. In this case protection against electric shock must be provided by the installation methods of the user. Only for use with single wires according to CSA approval.
Pack contents	Cable tie is included within the delivery

Technical characteristics

Limiting temperature	-30 ... +90 °C
Number of relockings	<10
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (accessories)	Polyamide (PA)
Colour (accessories)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Specifications
EN 45545-2 R22: HL1, HL2, HL3
EN 45545-2 R23: HL1, HL2, HL3
EN 45545-2 R24: HL1, HL2, HL3
IEC 61373 Category 1 Class B

UL / CSA
UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076
Please contact your local HARTING subsidiary for further information.

Commercial data

Packaging size 1

Net weight 5 g

Country of origin Germany

European customs tariff number 85366990

eCl@ss 27440392 Connector (accessories)