

Han-Eco cable gland M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 5131
Specification	Han-Eco cable gland M32
HARTING eCatalogue	https://b2b.harting.com/19410005131

Identification

Category	Accessories
Series of hoods/housings	Han-Eco®
Type of accessory	Cable gland

Technical characteristics

Tightening torque	15 Nm Fitting 4 Nm Cap nut
Wrench size	36
Limiting temperature	-40 ... +125 °C
Size	M32
Clamping range	13 ... 21 mm

Material properties

Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Commercial data

Packaging size	2
Net weight	33.7 g
Country of origin	Germany
European customs tariff number	39174000
eCl@ss	27144432 Screwed cable gland (electr.)