

## Han D M Crimpkontakt 0,14-0,37 mm<sup>2</sup> CuNi



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 6161
Specification	Han D M Crimpkontakt 0,14-0,37 mm <sup>2</sup> CuNi
HARTING eCatalogue	<a href="https://b2b.harting.com/09150006161">https://b2b.harting.com/09150006161</a>

### Identification

Category	Contacts
Series	Han D <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Operating current	≤10 A
Contact resistance	≤1 mΩ
Stripping length	8 mm

### Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
-----------------------	----

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	25
Net weight	0.7 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors