

## Han-Eco Mod.16-C-f. HBM/HSM-cord



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 016 5404
Specification	Han-Eco Mod.16-C-f. HBM/HSM-cord
HARTING eCatalogue	<a href="https://b2b.harting.com/19410165404">https://b2b.harting.com/19410165404</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® Modular
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings for cable to cable housing With fixing cord (cable shoe)

### Version

Locking type	Double locking lever
Size	16 B

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance

## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	60 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors