

Han 10B-Metallkappe



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 010 5404
Specification	Han 10B-Metallkappe
HARTING eCatalogue	https://b2b.harting.com/09300105404

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of accessory	Protection cover
Description of the accessory	for bearing pedestal

Version

Locking type	Single locking lever
Size	10 B

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (accessories)	Metal
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Commercial data

Packaging size	1
Net weight	59.9 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors