

## Han Snap Plastic Housing Size 16B



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 016 0401
Specification	Han Snap Plastic Housing Size 16B
HARTING eCatalogue	<a href="https://b2b.harting.com/09330160401">https://b2b.harting.com/09330160401</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Snap®
Type of hood/housing	Shell housing

### Version

Locking type	Snap-in latches
Size	16 B
Version	Top/side entry
Details	Size 16 A by using the corresponding adapter!
Pack contents	2 half shells with blind plugs

### Technical characteristics

Tightening torque	0.8 Nm
Limiting temperature	-40 ... +125 °C
Retention force	≥300 N locked condition

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

## Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate

## Specifications and approvals

Specifications	IEC 60068-2-6 Vibration (sinusoidal) IEC 60068-2-27 Shock
----------------	--

## Commercial data

Packaging size	1
Net weight	79 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors