

Han® S-HBM w.MC black busbar



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 001 0303
Specification	Han® S-HBM w.MC black busbar
HARTING eCatalogue	https://b2b.harting.com/09930010303

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® S
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	incl. male contact with busbar termination

Version

Locking type	Single locking lever
Number of contacts	1
Field of application	Energy Storage Systems

Technical characteristics

Rated current	200 A
Rated voltage	1,500 V
Rated impulse voltage	8 kV
Pollution degree	2
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 0.3 \text{ m}\Omega$
Limiting temperature	-40 ... +125 °C
Number of relockings	≥ 500
Degree of protection acc. to IEC 60529	IP40 mated condition IP20 unmated condition (1500 V DC; 1000 V AC)



Pushing Performance

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
	UL 1973
	UL 4128
	UL 9540
	UL 1977

Commercial data

Packaging size	1
Net weight	50.13 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors