




Pushing Performance

## Han 10B-asg2-K-29 (Ak in Al)



Part number	09 30 010 2263
Specification	Han 10B-asg2-K-29 (Ak in Al)
HARTING eCatalogue	<a href="https://b2b.harting.com/09300102263">https://b2b.harting.com/09300102263</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Surface mounted housing
Description of hood/housing	With metal cover
Type	High construction

### Version

Locking type	Double locking lever (on the hood)
Size	10 B
Version	Side entry
Cable entry	2x Pg 29
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR



Pushing Performance

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
CE	Yes

## Commercial data

Packaging size	1
Net weight	343 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors