

# Han-Yellock 60M-hood-M32 straight



Part number	11 13 600 1402
Specification	Han-Yellock 60M-hood-M32 straight
HARTING eCatalogue	https://b2b.harting.com/11136001402

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock <sup>®</sup>
Type of hood/housing	Shell

#### Version

Locking type	Push button
Size	Han-Yellock <sup>®</sup> 60
Version	Top entry
Cable entry	1x M32
Field of application	Hoods/housings for outdoor applications

#### Technical characteristics

Limiting temperature	-40 +125 °C
Un-/locking temperature	-10 +85 °C
Degree of protection acc. to IEC 60529	IP65
	IP67

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7021 (black grey)
RoHS	compliant
ELV status	compliant



## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

# Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
CE	Yes

## Commercial data

Packaging size	1
Net weight	153 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors