

Han® S-HA (16mm)-red



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 001 0502
Specification	Han® S-HA (16mm)-red
HARTING eCatalogue	https://b2b.harting.com/09930010502

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® S
Type of hood/housing	Hood
Description of hood/housing	Angled

Version

Locking type	Single locking lever
Number of contacts	1
Field of application	Energy Storage Systems
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	25 ... 50 mm ²
Conductor cross-section	AWG 4 ... AWG 1/0
Rated current	200 A
Rated voltage	1,500 V
Rated impulse voltage	8 kV
Pollution degree	2
Insulation resistance	>10 ⁸ Ω
Limiting temperature	-40 ... +125 °C
Number of relockings	≥500



Pushing Performance

Technical characteristics

Degree of protection acc. to IEC 60529	IP40 mated condition IP20 unmated condition (1500 V DC; 1000 V AC)
--	---

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 3001 (signal red)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
	UL 1973
	UL 4128
	UL 9540
	UL 1977

Commercial data

Packaging size	1
Net weight	20.37 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors