

Han-Modular Compact side entry M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 14 001 0501
Specification	Han-Modular Compact side entry M25
HARTING eCatalogue	https://b2b.harting.com/19140010501

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® Compact
Type of hood/housing	Hood

Version

Locking type	Single locking lever
Size	Modular Compact
Version	Side entry
Cable entry	1x M25
Pack contents	4 screws are included within the delivery

Technical characteristics

Tightening torque	1 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 locked condition

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61984
CE	Yes

Commercial data

Packaging size	10
Net weight	89.75 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors