



Pushing Performance

Han-Eco 16B-Cover-w. SL-w. cord-HTE/HSE



Part number	19 43 016 5442
Specification	Han-Eco 16B-Cover-w. SL-w. cord-HTE/HSE
HARTING eCatalogue	https://b2b.harting.com/19430165442

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Protection cover
Description of hood/housing	for hoods

Version

Locking type	Single locking lever
Size	16 B

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance

Material properties

Material flammability class acc. to UL 94
(locking levers) V-0

RoHS compliant

ELV status compliant

China RoHS e

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Specifications IEC 61984
EN 45545-2 R22: HL1, HL2, HL3
EN 45545-2 R23: HL1, HL2, HL3
EN 45545-2 R24: HL1, HL2, HL3

Commercial data

Packaging size 1

Country of origin Germany

European customs tariff number 85389099

eCl@ss 27440208 Cap for industrial connectors