



Pushing Performance

## Han CGM-M M40x1,5 D.19-28mm E.47



Part number	19 00 000 5078
Specification	Han CGM-M M40x1,5 D.19-28mm E.47
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005078">https://b2b.harting.com/19000005078</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-M
Type of accessory	Cable gland

### Technical characteristics

Wrench size	43 40
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M40
Clamping range	19 ... 28 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated

### Specifications and approvals

Approvals	DNV GL
-----------	--------

### Commercial data

Packaging size	1
Country of origin	Germany



Pushing Performance

## Commercial data

European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)