

## Han CGM-M-Rail M25 D.11-14.5mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 7122
Specification	Han CGM-M-Rail M25 D.11-14.5mm
HARTING eCatalogue	<a href="https://b2b.harting.com/19000007122">https://b2b.harting.com/19000007122</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-M-Rail
Type of accessory	Cable gland
Description of the accessory	Railway version

### Technical characteristics

Tightening torque	≤7 Nm (depending on the cable and the seal insert used)
Wrench size	27 30
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68
Size	M25
Clamping range	11 ... 14.5 mm
Width across corners	32.9 mm

### Material properties

Material (seal)	EPDM
Material (cable glands)	Brass
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

## Material properties

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances Yes

REACH SVHC substances Lead

## Specifications and approvals

Approvals DNV GL

## Commercial data

Packaging size 10

Net weight 0.1 g

Country of origin Germany

European customs tariff number 84849000

eCl@ss 27144432 Screwed cable gland (electr.)