

Han Q 4/2-F Insert AS 2,5-6mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 006 2765
Specification	Han Q 4/2-F Insert AS 2,5-6mm ²
HARTING eCatalogue	https://b2b.harting.com/09120062765

Identification

Category	Inserts
Series	Han [®] Q
Identification	4/2

Version

Termination method	Axial screw termination
Gender	Female
Size	Han-Compact [®]
Number of contacts	4
PE contact	Yes
Details	Without signal contacts

Technical characteristics

Conductor cross-section	2.5 ... 6 mm ²
Rated current	40 A
Rated voltage conductor-earth	400 V
Rated voltage conductor-conductor	690 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤0.3 mΩ
Tightening torque	1.8 Nm
Limiting temperature	-40 ... +125 °C



Pushing Performance

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	36.5 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors