



Quality Products. Service Excellence.

Mounting Rails *HLPUR Series*

Compatible with HLP, HLPB and ERP Series

Features



- Constructed in 14-gauge steel
- Sold in pairs
- EIA compliant 10-32 threaded or round hole punched mounting rails.
- Rails come stamped and numbered in 1U (1.75") increments.
- For use with **HLP**, **HLPB** and **ERP** Series.
- Finished in smooth powder paint.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

- 10-32 Rack Rail Clip Nuts
- Mounting Hardware

Rotating Rails

Part No.	Mounting Dimensions		Rack Units	Rotation	EIA Rail Type	Paint Finish
	Height	Width				
HLP2UR	3.50	19.00	2U	180 Degrees	10-32 Threaded	Smooth White
HLP4UR	7.00	19.00	4U	180 Degrees	Clip Nut Round Hole	Smooth Black
HLP6UR	10.50	19.00	6U	180 Degrees	Clip Nut Round Hole	Smooth Black
HLP8UR	14.00	19.00	8U	180 Degrees	Clip Nut Round Hole	Smooth Black

Fixed Five (5) Position Rails

Part No.	Mounting Dimensions		Rack	Rotation	EIA	Paint
	Height	Width	Units		Rail Type	Finish
HLP2UFR	3.50	19.00	2U	Fixed five (5) positions	Threaded 10-32	Smooth White
HLP4UFR	7.00	19.00	4U	Fixed five (5) positions	Threaded 10-32	Smooth White
HLP6UFR	10.50	19.00	6U	Fixed five (5) positions	Threaded 10-32	Smooth White
HLP8UFR	14.00	19.00	8U	Fixed five (5) positions	Threaded 10-32	Smooth White

Data subject to change without notice

© 2023. Hammond Manufacturing Ltd. All rights reserved.