

Han CGM-M-Rail M20 D.7-10mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 7120
Specification	Han CGM-M-Rail M20 D.7-10mm
HARTING eCatalogue	https://b2b.harting.com/19000007120

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-M-Rail
Type of accessory	Cable gland
Description of the accessory	Railway version

Technical characteristics

Tightening torque	≤6 Nm (depending on the cable and the seal insert used)
Wrench size	22 24
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68
Size	M20
Clamping range	7 ... 10 mm
Width across corners	26.4 mm

Material properties

Material (seal)	EPDM
Material (cable glands)	Brass
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

Material properties

REACH Annex XVII substances	No
-----------------------------	----

REACH ANNEX XIV substances	No
----------------------------	----

REACH SVHC substances	Yes
-----------------------	-----

REACH SVHC substances	Lead
-----------------------	------

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
----------------	----

Net weight	0.1 g
------------	-------

Country of origin	Germany
-------------------	---------

European customs tariff number	84849000
--------------------------------	----------

eCl@ss	27144432 Screwed cable gland (electr.)
--------	--