

Uni-Dicht-Verschr. Pg21, 20,5-17,0mm sw



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5158
Specification	Uni-Dicht-Verschr. Pg21, 20,5-17,0mm sw
HARTING eCatalogue	https://b2b.harting.com/09000005158

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Cable gland
Description of the accessory	for hoods for cable to cable housing

Technical characteristics

Tightening torque	≤8 Nm (depending on the cable and the seal insert used)
Wrench size	33
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65
Size	Pg 21
Clamping range	17 ... 20.5 mm

Material properties

Material (cable glands)	Thermoplastic
Colour (accessories)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead

Commercial data

Packaging size	10
Net weight	10.24 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)