




Han 16B-HSE-NPTF 3/4 Zoll



| | |
|--------------------|---|
| Part number | 09 30 516 1520 |
| Specification | Han 16B-HSE-NPTF 3/4 Zoll |
| HARTING eCatalogue | https://b2b.harting.com/09305161520 |

Identification

| | |
|--------------------------|--------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] B |
| Type of hood/housing | Hood |
| Type | Low construction |

Version

| | |
|----------------------|---|
| Locking type | Double locking lever |
| Size | 16 B |
| Version | Side entry |
| Cable entry | 1x NPTF 3/4" |
| Field of application | Standard hoods/housings for industrial connectors |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65 |

Material properties

| | |
|-----------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |



Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Approvals DNV GL

UL / CSA UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076

CE Yes

Commercial data

Packaging size 1

Net weight 195 g

Country of origin China

eCl@ss 27440202 Shell for industrial connectors