

8			7			6		
PIN #	COLOR	AWG	PIN #	COLOR	AWG			
1	BLACK	24AWG	14	GREEN	24AWG			
2	BLACK/WHITE	24AWG	15	GREEN/BLACK	24AWG			
3	BROWN	24AWG	16	GREEN/WHITE	24AWG			
4	BROWN/WHITE	24AWG	17	BLUE	24AWG			
5	RED	24AWG	18	BLUE/WHITE	24AWG			
6	RED/BLACK	24AWG	19	VIOLET	24AWG			
7	RED/WHITE	24AWG	20	VIOLET/WHITE	24AWG			
8	ORANGE/BLACK	24AWG	21	GRAY	24AWG			
9	ORANGE	24AWG	22	GRAY/BLACK	20AWG			
10	ORANGE/WHITE	24AWG	23	PINK	20AWG			
11	YELLOW	24AWG	24	PINK/BLACK	20AWG			
12	YELLOW/BLACK	24AWG	25	WHITE	20AWG			
13	LIGHT GREEN	24AWG						

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/26/2012	BEM




TABLE A	
P/N	L
DB25-MFP-2M	2M [79"]
DB25-MFP-3M	3M [118"]
DB25-MFP-5M	5M [197"]
DB25-MFP-6M	6M [236"]
DB25-MFP-10M	10M [393"]
DB25-MFP-12M	12M [472"]

NOTES:
CABLE: 24/21 & 20/4 SHIELDED CABLE WITH 20AWG DRAIN
FULL LENGTH MYLAR FOIL SHIELD
FULLY WIRED STRAIGHT THRU

SHIELD & 20 AWG DRAIN CONNECTED TO METAL SHELL
BRASS NICKEL PLATED THUMB SCREWS

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
MENCOM CORPORATION. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
MENCOM CORPORATION IS
PROHIBITED.

		UNLESS OTHERWISE SPECIFIED:		NAME	MENCOM CORPORATION				
		DIMENSIONS ARE IN MM AND [INCHES]	DRAWN	CAM				TITLE: DB25 MALE/FEM EXT CABLE GUARANTEED COLOR CODE	
			CHECKED						
			ENG APPR.						
			MFG APPR.						
			Q.A.		SIZE B	DWG. NO. DB25-MFP-ZZ	REV A		
		MATERIAL	COMMENTS:						
		FINISH							
		DO NOT SCALE DRAWING	SCALE: 1:1					WEIGHT:	SHEET 1 OF 1