

PIN #	COLOR
1	WHITE w/ORANGE
2	WHITE w/GREEN
3	ORANGE
4	GREEN




TABLE A	
P/N	L
MDE45-4MMP-1M	40" [1m]
MDE45-4MMP-2M	79" [2m]
MDE45-4MMP-3M	118" [3m]
MDE45-4MMP-4M	157" [4m]
MDE45-4MMP-5M	197" [5m]
MDE45-4MMP-6M	236" [6m]
MDE45-4MMP-8M	315" [8m]
MDE45-4MMP-10M	393" [10m]

<b>MATERIALS:</b>	
BODY:	BLACK PVC
CABLE:	2 PR 24/2 CAT 5e CABLE
COUPLING:	NICKEL PLATED BRASS
INSERT:	POLYAMIDE
CONTACTS:	GOLD PLATED COPPER ALLOY

**PROPRIETARY AND CONFIDENTIAL**  
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MENCOM CORPORATION. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MENCOM CORPORATION IS PROHIBITED.

VOLTS	300V
AMPS	4A
TEMP:	80°C

UNLESS OTHERWISE SPECIFIED:	DRAWN BY	ADM
DIMENSIONS ARE IN INCHES AND [MM]	DRAWN DATE	09/22/2016
	CHECKED BY	
	CHECK DATE	
	COMMENTS:	
MATERIAL		
FINISH		
DO NOT SCALE DRAWING		

MENCOM CORPORATION		
TITLE:		
SIZE	DWG. NO.	REV
<b>B</b>	MDE45-4MMP-ZZ	<b>A</b>
SCALE: 1.5:1	WEIGHT:	SHEET 1 OF 1