



PIN #	COLOR
1	BROWN
2	BLUE
GND	GREEN / YELLOW

REVISIONS		
REV.	DESCRIPTION	DATE
A	REDRAWN IN SW	3/18/2005



SCREW AND FLAT GASKET SUPPLIED WITH EACH CABLE



P/N	L	STD?
VCG-120-00	40" [1M]	NO
VCG-220-00	79" [2M]	YES
VCG-320-00	118" [3M]	NO
VCG-420-00	157" [4M]	NO
VCG-520-00	197" [5M]	YES
VCG-620-00	236" [6M]	NO
VCG-A20-00	393" [10M]	YES

PARTS LISTED AS NOT BEING STANDARD MAY REQUIRE MINIMUM ORDERS

MATERIALS	
BODY:	BLACK POLYAMIDE
CONTACTS:	SILVER PLATED COPPER ALLOY
CABLE:	BLACK 20/3 OIL RESISTANT
GASKET:	THERMOPLASTIC
SCREW:	ZINC PLATED STEEL

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MENCOM CORPORATION. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MENCOM CORPORATION IS PROHIBITED.

VOLTS	24V
AMPS	10A
TEMP:	90°C

UNLESS OTHERWISE SPECIFIED:	DRAWN BY	ADM
DIMENSIONS ARE IN INCHES AND [MM]	DRAWN DATE	09/22/2016
	CHECKED BY	
	CHECK DATE	
	COMMENTS:	
MATERIAL		
FINISH		
DO NOT SCALE DRAWING		

MENCOM CORPORATION		
TITLE: DIN C 24V MOV LED 2+E		
SIZE	DWG. NO.	REV
B	VCG-ZZ20-00	A
SCALE: 2:1	WEIGHT:	SHEET 1 OF 1