

Product data sheet

Characteristics

HOM245GFI

Mini circuit breaker, Homeline, 45A, 2 pole, 120/240VAC, 10kA AIR, ground fault class A, plug in, UL



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	45 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Short Circuit Current Rating	10 kA
Number of Spaces	2
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	AWG 12...AWG 4 aluminium)1

Complementary

Tightening torque	40.71 lbf.in (4.6 N.m) 0.00...0.02 in ² (2.5...10 mm ²) (AWG 16...AWG 14)
Height	4.23 in (107.44 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature for Operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	00147-HOM 2 POLE GFI CB,40A MAX
Discount Schedule	DE3D
GTIN	785901508243
Nbr. of units in pkg.	1
Package weight(Lbs)	1.21 lb(US) (0.549 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.20 in (5.588 cm)
Package 1 width	3.60 in (9.144 cm)
Package 1 Length	5.30 in (13.462 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information