



Ethernet Series Etherlink RJ45 Cordsets

8 Conductor Ethernet Series RJ45 Cordsets



Double Ended Cordsets | 42 VDC, 1.5 amps | CAT5e/CAT6a | Strain Relief | IP20 Rating




RJ45 Male to Male Plug with No Strain Relief							
# of Poles	Front View	Wire AWG Rating	Cable Standard	Cables	Shield Type	Jacket Color	Part Number
8		24 AWG 42 VDC 1.5 A	CAT5e	PVC	N/A	Gray	RJ45-*
				PUR	N/A	Gray	RJ45P-**
RJ45 Male to Male Plug with Over-Molded Strain Relief							
8		24 AWG 42 VDC 1.5 A	CAT5e	PVC Over-Molded	N/A	Blue	RJ45-IC-*-BU
						Red	RJ45-IC-*-RD
						Black	RJ45-IC-*-BK
						Gray	RJ45S-IC-*-GY
			Foil Shield to RJ45 Connectors	Blue	RJ45S-IC-*-BU		
CAT6a	PVC Over-Molded	N/A	Blue	RJ45C6-IC-*-BU			
RJ45 Male to Male Plug with Strain Relief							
4		24 AWG 42 VDC 1.5 A	CAT5e	PVC	N/A	Teal	RJ45-4MMP-**
				PVC	Foil Shield to RJ45 Connectors	Teal	RJ45S-4MMP-**
				PUR	Foil & Braided Shield to RJ45 Connectors	Teal	RJ45SP-4MMP-**
				TPE	Foil & Braided Shield to RJ45 Connectors	Teal	RJ45SW-4MMP-**
8		24 AWG 42 VDC 1.5 A	CAT5e	PVC	N/A	Teal	RJ45-8MMP-**
				PUR	N/A	Teal	RJ45P-8MMP-**
				PUR	Foil & Braided Shield to RJ45 Connectors	Teal	RJ45SP-8MMP-**
				TPE	Foil & Braided Shield to RJ45 Connectors	Teal	RJ45SW-8MMP-**
		26 AWG 42 VDC 1.5 A	CAT5e	PVC	Foil Shield to RJ45 Connectors	Blue	RJ45S-8MMP-**
			CAT6a	PVC	Foil Shield to RJ45 Connectors	Blue	RJ45C6-8MMP-**

* Lengths in feet. Standard cable lengths are 1, 3, 7, 10, 15, 20, 25 & 50 feet. Consult factory for other lengths.

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.


Cable specifications on Page L-22~23 apply to only 24 AWG 4MMP & 8MMP cables in the table.



RJ45 Male to Male Plug



Over-Molded RJ45 Male to Male Plug



RJ45 Male to Male Plug with Strain Relief