

PRODUCT-DETAILS

BT4-G

PVC CTD MGL T COND BODY 1-1/4IN GRY



General Information

Extended Product Type	BT4-G
Product ID	7TAA087280R0018
EAN	0704508356576
Catalog Description	PVC CTD MGL T COND BODY 1-1/4IN GRY
Long Description	PVC Double-Coated Mogul Conduit Body, T Style, Pipe Size 1-1/4 Inch/35 Metric, Body and Cover Dark Gray Iron with Electro Galvanized Finish, Dark Gray

Additional Information

Application	Act As Pull Outlets for Conductors that are Stiff, Due to Large Size or Type of Insulation
Product Type	Mogul Conduit Outlet Bodies & Covers

Ordering

EAN	0704508356576
UPC	704508356576

Dimensions

Product Net Depth / Length	9.56 in
----------------------------	---------

Technical

Number of Batteries	0
Color	Dark Gray
Material	Iron

Environmental

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	1 in 25 mm

Certificates and Declarations

Data Sheet, Technical Information	BT4-G
Instructions and Manuals	BT4-G

Classifications

ETIM 8	EC003618 - Form part for installation tubes
UNSPSC	39131708

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Rigid Cable Protection Systems

