



IPL1/0-3C SHOWN

PART NUMBER	NO. OF PORTS	LENGTH
IPL1/0-3C	3	2.24
IPL1/0-4C	4	2.89
IPL1/0-5C	5	3.54
IPL1/0-6C	6	4.19
IPL1/0-8C	8	5.49
IPL1/0-10C	10	6.79
IPL1/0-12C	12	8.09
IPL1/0-14C	14	9.39

WIRE ENTRY PORT
WIRE RANGE: 1/0 - #14 AWG
PRE-FILLED W/ OXIDE INHIBITOR

NOTES:

1. CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
2. UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
3. DUAL RATED FOR 90°C COPPER AND/OR ALUMINUM CONDUCTOR.
4. COLD TEMPERATURE RATED TO -45°C.
5. HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION AND CHEMICAL RESISTANT.

CONTACT NSi FOR SALES @ 800.321.5847

		POLARIS SALES . CO . INC	
		11625 PROSPEROUS DRIVE ODESSA, FL 33556	
PROPRIETARY AND CONFIDENTIAL		TITLE: <h2> CLEAR INSULATED 1/0 CONNECTOR </h2>	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.		DWG. NO. <h2> IPL1/0C SERIES </h2>	
DRAWN BY T.MITCHELL	NAME T.MITCHELL	DATE 11/29/2021	
MATERIAL: N/A		SCALE: N/A	SHEET: 1 OF 1