

B1

**Pan-Ty® Wing Push Mount Ties – Nylon 6.6**


- For indoor use
- Cable tie, mount, and fastener in a single part
- Used to attach bundles to another surface such as a flat panel
- Anchor is easily pressed into a pre-formed hole and locks in place
- Wings provide constant tension for a stable, secure, and rattle-free installation
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

B3


C1




C2



C3



C4



D1



D2



D3



E1

Part Number	Length		Width		Thickness		Nominal Hole Dia.		Max. Panel Thickness		Max. Bundle Dia.		Min. Loop Tensile Str.		Recommended Installation Tool	Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	Lbs.	N			

**Miniature Cross Section**

E2

<b>PLWP1M-C</b>	4.3	109	0.098	2.5	0.044	1.1	0.187	4.7	0.093	2.4	0.87	22	18	80	GTS-E, GS2B-E, PTS, PPTS, STS2	100	1000
-----------------	-----	-----	-------	-----	-------	-----	-------	-----	-------	-----	------	----	----	----	--------------------------------------	-----	------

**Intermediate Cross Section**

E3

<b>PLWP1.5I-C</b>	6.0	152	0.135	3.4	0.045	1.2	0.187	4.7	0.093	2.4	1.25	32	40	178	GTS-E, GS2B-E, PTS, PPTS, STS2	100	1000
-------------------	-----	-----	-------	-----	-------	-----	-------	-----	-------	-----	------	----	----	-----	--------------------------------------	-----	------

**Standard Cross Section**

E4

<b>PLWP1S-C</b>	5.2	132	0.190	4.8	0.052	1.3	0.250	6.4	0.105	2.7	1.00	25	50	222	GTS-E, GS2B-E, GTH-E, GS4H-E, PTS, PTH, PPTS, STS2, STH2	100	1000
<b>PLWP1SA-D</b>	5.1	130	0.190	4.8	0.052	1.3	0.187	4.7	0.093	2.4	1.00	25	50	222		500	5000
<b>PLWP1SB-D</b>	5.2	132	0.190	4.8	0.052	1.3	0.187	4.7	0.157	4.0	1.00	25					
<b>PLWP1.5S-D</b>	6.8	173	0.190	4.8	0.052	1.3	0.250	6.4	0.105	2.7	1.50	38	50	222		100	1000
<b>PLWP1.5SA-D</b>	6.7	170	0.190	4.8	0.052	1.3	0.187	4.7	0.093	2.4	1.50	38					
<b>PLWP2S-C</b>	7.8	198	0.190	4.8	0.052	1.3	0.250	6.4	0.105	2.7	1.75	45	50	222		500	5000
<b>PLWP2SA-D</b>	7.7	196	0.190	4.8	0.052	1.3	0.187	4.7	0.093	2.4	1.75	45	50	222			
<b>PLWP2SB-D</b>	7.8	198	0.190	4.8	0.052	1.3	0.187	4.7	0.157	4.0	1.75	45					

F

**Light-Heavy Cross Section**

G

<b>PLWP2H-TL</b>	8.9	226	0.300	7.6	0.075	1.9	0.266	6.8	0.105	2.7	2.00	51	120	534	GTH-E, GS4H-E, GS4EH-E, PTH, STH2, ST3EH	250	2500
<b>PLWP3H-TL</b>	12.0	305	0.300	7.6	0.075	1.9	0.266	6.8	0.105	2.7	3.00	76					

Note: UL Recognized and CSA Certified except PLWP2H/3H.

H