



PANDUIT PART #	WIRE RANGE		CRIMPING LENGTH	COMPRESSED AIR SUPPLY	WEIGHT
	AWG	[mm ²]			
CTFP-25	24-14	0.25-2.5	6 - 12 mm	5 bar / 72 psi	2.8kg / 6.2 lb
CTFP-40	24-12	0.25-4	6 -12 mm	5 bar / 72 psi	
CTFP-100	12-8	4-10	6 -12 mm	5 bar / 72 psi	

NOTES:

THE CTFP SERIES CRIMP TOOLS ARE PNEUMATIC FERRULE CRIMPING PRESSES INTENDED TO BE USED WITH LOOSE PIECE FERRULES.

GO TO PANDUIT.COM FOR A LIST OF PRODUCTS THAT ARE COMPATIBLE WITH THIS UNIT.

OVERALL APPROXIMATE DIMENSIONS:

CRIMPING UNIT: 2.75"H x 5.5"W x 7"L
 FOOT PEDAL: 5.5"H x 6"W x 8.5"L

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL	DRAWING NUMBER	SIZE
							PNEUMATIC FERRULE CRIMPING TOOL	N/A	00090FPA_DC	B
							CUSTOMER DRAWING			
							ITEM REVISION NAME 00090FPA/02			
							DATASET FILE NAME 00090FPA/01_DC/00A			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			
							.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °			
							THIRD ANGLE PROJECTION			
							DRAWN BY FCHE			
							DATE 8/30/2018			
							CHK TMR			
							SCALE N/A			
									SHT 1 OF 1	



D10100DB/17