



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A IN. (mm)	B IN. (mm)	C IN. (mm)	D IN. (mm)	E IN. (mm)	WRITE-ON AREA IN. (mm)	CROSS- SECTION	WEIGHT lbs./ 100 (g) pcs.
	MIN. IN (mm)	MAX. IN (mm)								
CM4S	.25 (6.4)	4.38 (111)	.033 (.84)	.75 (19.1)	3.88 (98.5)	1.50 (38.1)	15.25 (387)	1.50 x 2.62 (38.1 x 66.5)	STANDARD	1.59 (721)

NOTES:

- SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR. FIGURE 1
- APPLICATION INSTRUCTIONS: LOOP STRAP THRU "V" SHAPED NOTCH NEAR STRAP BODY FOR FLAG TIE AND AWAY FROM STRAP BODY FOR MARKER TIE. LOOP EXCESS THRU SLOT NEXT TO "V" SHAPED NOTCH. (SEE FIGURE 1)

DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
3	5/20/13	BWG	KJM	RTFI	TITLE BORDER REDRAWN, UPDATED NOTE 1.	SS-18576/03	BWG	5/20/13	RTFI	NONE		A

TITLE CABLE MARKER STRAP-CM4S	
CONTROL DRAWING	
ITEM REVISION NAME 10B015JP/00	PANDUIT
DATASET FILE NAME 10B015JP/00 - SS-18576-REV03	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)	
.X : .XX :	.XXX : ANGLES :
THIRD ANGLE PROJECTION	
DRAWING NUMBER: SS-18576	
MATERIAL: POLYETHYLENE	

D:\10100DA\15