


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PRT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.78 (19.8)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PRT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.78 (19.8)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PRT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.78 (19.8)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PRT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.78 (19.8)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2233)
PRT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.78 (19.8)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PRT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.78 (19.8)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.
DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	MATERIAL:	DRAWING NUMBER:
							PAN-TY® RELEASABLE LASHING TIES			PANDUIT	
							CUSTOMER DRAWING	10B015LA/02	10B015LA/02 SS-6507_REV10	NYLON 6.6	
10	7/23/21	BWG	MPH	JADE	REVISED "E" WIDTH	099443/00	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)				
9	11/05/13	BWG	RTFI	KJM	CORRECTED TOLERANCES.	SS-6507/09	.x ± .1 (2.5) .xxx ± .010 (.25) .xx ± .02 (.5) ANGLES ± -----				
8	10/24/13	BWG	RTFI	KJM	UPDATED TITLE BORDER AND NOTE ONE.	SS-6507/08	THIRD ANGLE PROJECTION				SS-6507
							DRAWN BY: L.VALDES DATE: 7-15-77 CHK: HVP SCALE: NONE				SHT 1 OF 1
											SIZE: A

D110100DA/16