

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER SYSTEM

HSTT 12-48 Q 2

COLOR:

BLANK = BLACK	5 = GREEN
1 = BROWN	6 = BLUE
2 = RED	10 = WHITE
3 = ORANGE	45 = YELLOW/GREEN
4 = YELLOW	C = CLEAR

QUANTITY PER CARTON (48 IN ONLY)

Q = 25 PCS
 5 = 5 PCS
 2 = 2 PCS


LENGTH INCHES [mm]

48 = [1219]	M = 1000 [304.8]
Y = [152.4]	D = 500 [152.4]
	T = 200 [61]
	C = 100 [30.5]
	L = 50 [15.2]
	Q = 25 [7.6]

TUBING SIZE - EXPENDED I.D. (SEE CHART)

TT = THIN WALL

TTV = THIN WALL VW-1 RATED



HEAT SHRINK TUBING SIZE	MIN. EXPANDED I.D. IN [mm]	MAX. RECOVERED I.D. IN [mm]	NOMINAL REC. WALL THICKNESS IN [mm]
05	0.046 [1.2]	0.023 [.6]	0.016 ± 0.003 [0.406 ± 0.076]
06	0.063 [1.6]	0.031 [.8]	0.017 ± 0.003 [0.432 ± 0.076]
09	0.093 [2.4]	0.046 [1.2]	0.020 ± 0.003 [0.508 ± 0.076]
12	0.125 [3.2]	0.062 [1.6]	0.020 ± 0.003 [0.508 ± 0.076]
19	0.187 [4.8]	0.093 [2.4]	0.020 ± 0.003 [0.508 ± 0.076]
25	0.250 [6.4]	0.125 [3.2]	0.025 ± 0.003 [0.635 ± 0.076]
38	0.375 [9.5]	0.187 [4.8]	0.025 ± 0.003 [0.635 ± 0.076]
50	0.500 [12.7]	0.250 [6.4]	0.025 ± 0.003 [0.635 ± 0.076]
75	0.750 [19.1]	0.375 [9.5]	0.030 ± 0.003 [0.762 ± 0.076]
100	1.000 [25.4]	0.500 [12.7]	0.035 ± 0.005 [0.889 ± 0.127]
150	1.500 [38.1]	0.750 [19.1]	0.040 ± 0.006 [1.016 ± 0.152]
200	2.000 [50.8]	1.000 [25.4]	0.045 ± 0.007 [1.143 ± 0.178]
300	3.000 [76.2]	1.500 [38.1]	0.050 ± 0.008 [1.270 ± 0.203]
400	4.000 [101.6]	2.000 [50.8]	0.055 ± 0.009 [1.397 ± 0.229]

NOTES:

- MATERIAL: CROSSLINKED POLYOLEFIN
- SHRINK RATIO: 2:1
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE)."
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX.
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVLENT [mm]
- REELS OF THE PRODUCT ARE ALLOWED TO HAVE SPLICES.

PACK CODE	M	D	T	C	L	Q
ALLOWED SPLICES	4	3	2	1	1	0



TITLE THIN WALL HEAT SHRINK TUBING (HSTT / HSTTV) CUSTOMER DRAWING						
ITEM REVISION NAME G035970M/00						
DATASET FILE NAME G035970M_DC_GB0239KH_REV03/00A						
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .05 [1.3] .xxx ± .010 [.25] .xx ± .02 [.5] ANGLES ± 5 °					MATERIAL: SEE NOTES	
DRAWING NUMBER: GB0239KH					DRAWING NUMBER: GB0239KH	
DRAWN BY LGRAVITT	DATE 05-12-03	CHK	SCALE N.T.S.	SHT 1 OF 1		SIZE A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	07-29-15	JBN	MRJS	RGRO	F. UPDATED DRAWING TO CURRENT STANDARDS AND REMOVED PRIOR REVISION MARKS	GB0239KH

D101000A/16