



IPLD500-5C SHOWN

PART NUMBER	NO. OF PORTS	LENGTH
IPLD500-3C	3	4.01
IPLD500-4C	4	5.16
IPLD500-5C	5	6.30
IPLD500-6C	6	7.45
IPLD500-8C	8	9.74
IPLD500-10C	10	12.03
IPLD500-12C	12	14.32
IPLD500-14C	14	16.61

WIRE ENTRY POINT
WIRE RANGE: 500MCM - #4AWG
PRE-FILLED W/ OXIDE INHIBITOR

NOTES:

- CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- DUAL RATED FOR 90C COPPER AND/OR ALUMINUM CONDUCTOR.
- COLD TEMPERATURE RATED TO -45C.
- HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION AND CHEMICAL RESISTANT



POLARIS
SALES . CO . INC

PROPRIETARY AND CONFIDENTIAL

11625 PROSPEROUS DRIVE ODESSA, FL 33556

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.

TITLE:

CLEAR INSULATED DUAL ENTRY 500 CONNECTOR

NAME	DATE
T.MITCHELL	12/2021

DWG. NO.

IPLD500C

MATERIAL: N/A

SCALE: N/A

SHEET: 1 OF 1