

ITEM NUMBER	PART NUMBER	DESCRIPTION	STANDARD PACKAGE QTY.
1	MP300	MP300 PRINTER	1
2	*MP300-ACS	120-240 VAC POWER SUPPLY MODULE WITH POWER CORD FOR NORTH AMERICA	1
3	*MP300-BATT	LITHIUM ION BATTERY	1
4	MP-USB	MP100/300 USB PRINTER CABLE	1
5	*S100X150VAM	MP CASSETTE, SELF-LAMINATING LABEL, VINYL, 1.00" W x 1.50" H, .50" PRINT ON AREA, CLEAR/ WHITE	1
6	IMPORTANT INFORMATION	PRINTED COPY OF IMPORTANT SAFETY INFORMATION SHEET	1
7	QUICK REFERENCE CARD	PRINTED COPY OF QUICK REFERENCE CARD IN THREE LANGUAGES (EN, FR, SP)	1
8	*MP300-CASE	HARD PLASTIC CARRYING CASE WITHOUT SLEEVE	1
9	MP300-MAGNET	SET OF TWO MAGNETIC ATTACHMENTS FOR MP300 PRINTER	1
10	BATTERY DIRECTIVE	BATTERY DIRECTIVE INSTRUCTIONS FOR LITHIUM ION BATTERY PACK	1



NOTES:
 1. * IN FRONT OF PART NUMBER DENOTES SELLABLE PANDUIT PART NUMBER.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01	1-21-2021	JSUN	RCMC	ALP	REMOVE * BEFORE MP300-MAGNET	094056/00
00	10-29-19	TMSA	RCMC	JHAC	INITIAL RELEASE	GAECNXXXX

TITLE		"MP300"	
PANDUIT MP300 MOBILE THERMAL TRANSFER PRINTER			
CUSTOMER DRAWING			
ITEM REVISION NAME	00406SBB/01		
DATASET FILE NAME	00406SBB_DC/01		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x : .1 [2.54]	.xxx : .005 [.127]	NONE	
.xx : .01 [.25]	ANGLES : 5 °	DRAWING NUMBER:	
THIRD ANGLE PROJECTION		00406SBB_DC	
DRAWN BY	DATE	CHK	SCALE
TMSA	10-29-19	JHAC	NTS
SHT 1 OF 1			SIZE
			B

D10100DB/17