


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	WIRE SIZE	COLOR CODE	COMPATIBLE WITH PANDUIT TOOL(S)	GO/NO-GO SPEC.
CD-2001-8-SET	#8 AWG	RED	CT-3001, CT-3001/CCP	.167/.217
CD-2001-6-SET	#6 AWG	BLUE		.197/.247
CD-2001-4-SET	#4 AWG	GRAY		.237/.287
CD-2001-2-SET	#2 AWG	BROWN		.297/.347
CD-2001-1-SET	#1 AWG	GREEN		.327/.377
CD-2001-1/0-SET	1/0 AWG	PINK		.373/.423
CD-2001-2/0-SET	2/0 AWG	BLACK		.409/.459
CD-2001-3/0-SET	3/0 AWG	ORANGE		.451/.501
CD-2001-4/0-SET	4/0 AWG	PURPLE		.503/.553
CD-2001-250-SET	250 kcmil	YELLOW		.539/.589
CD-2001-300-SET	300 kcmil	WHITE		.601/.651
CD-2001-350-SET	350 kcmil	RED		.671/.721
CD-2001-400-SET	400 kcmil	BLUE		.655/.705
CD-2001-500-SET	500 kcmil	BROWN		.655/.705
CD-2001-BG-SET	CTAP4-8 TO CTAP4-4	N/A		.497/.547
CD-2001-C-SET	CTAP2-2 TO CTAP2-4	N/A		.657/.707



INSTRUCTIONS:

WITH THE DIES INSERTED IN THE TOOL AND IN THE FULLY CLOSED POSITION, USE A CALIPER OR INSIDE MICROMETER TO MEASURE THE OPENING AT THE FURTHEST MOST POINT OF THE RADIUS (DIMENSION "X")

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	11/1/22	JHNU	JHNU	JADE	DRAWING RELEASED	127162

PRODUCT SPEC	N/A	PACKAGING SPEC	N/A
PART NUMBER	AS NOTED ABOVE	WORK INSTRUCTION	N/A
INSPECTION INSTRUCTION NUMBER	N/A	P/MEA & CONTROL PLAN NUMBER	N/A
CD-2001 DIE SETS GO/NO-GO SPECIFICATION CUSTOMER DRAWING			
ITEM REVISION NAME	02789NBE/00		
DATASET FILE NAME	02789NBE/00		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5°			
THIRD ANGLE PROJECTION			DRAWING NUMBER: 02789NBE-DC
DRAWN BY	DATE	CHK	SCALE
JHNU	11/1/22	JADE	NONE
SHT 1 OF 1			SIZE B

D101009B/17