


ITEM	QTY	PART NO.	DESCRIPTION
1	3	CA21689A01	RING, RETAINING
2	1	CA21688A01	SPRING, HANDLE RETURN
3	5	CA21492A01	CLIP, E
4	1	CA21687A01	SCR, HSBHC * M3
5	1	CA21686A01	PRELOAD ADJUSTING STAR
6	1	CA21685A01	PIN, RETAINING PAWL SPR.
7	1	CA21684A01	PIN, PIVOT PAWL
8	1	CA21683A01	PAWL
9	1	CA21491A01	SPRING, PAWL
10	1	CA21493B01	SET, HANDLE (UPP./LWR)
11	2	CA32115A01	SCR, HSBHC * M4 X 14



GRIP SPAN  
162.7 [6.4] FULLY OPEN REF.  
40.0 [1.6] FULLY CLOSED REF.

NOTES, UNLESS OTHERWISE SPECIFIED:

TOOL WEIGHT: 1.41 lbs/0.64 Kg


ALL DIMENSIONS IN METRIC (mm)  
[ ] DIMENSIONS IN INCHES

HANDLE TO SPRING RETURN FREELY TO OPEN POSITION AFTER CRIMPING

TOOL FRAME MEMBERS AND FASTENERS TO BE BLACK OXIDE FINISH.

RECOMMENDED LUBE FOR FRAME LINKAGE:  
MOLYKOTE BR2 PLUS. (SUPPLIER: DOW CORNING)

THE CRIMP POCKET INSPECTION INFORMATION IS LISTED IN THE OPERATING INSTRUCTIONS. THE OPERATING INSTRUCTIONS CAN BE FOUND ON THE WEB. GO TO WWW.PANDUIT.COM AND SEARCH FOR "TERMINAL LOOSE PIECE OPERATION MANUALS".



7.0  
[.3] REF. IN FULLY CLOSED POSITION

CRIMP POCKET AWG / mm <sup>2</sup>	ENGLISH		METRIC	
	GO / NO GO GAGE MEMBERS "G" Dia. (GO)	"NG" Dia. (NO GO)	GO / NO GO GAGE MEMBERS "G" Dia. (GO)	"NG" Dia. (NO GO)
22-14/0,5-2,5	.062"	.072"	1,57mm	1,83mm

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01	1/25/17	BWG	BJPU	JADE	REMOVED PANDUIT LOGO FROM GRIPS. MOVED "MADE IN" FROM THE GRIPS TO THE FRAME AND UPDATED THE LOGO ON THE TOOL FRAME. ADDED CHART.	004857/02
00	04-06-05	DCS	MBR	BKA	RELEASED	004857/00

TITLE		CD*CT-300-1	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		R24939BA/01	
DRAWING NUMBER		TP24939C01	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		DRAWING NUMBER	
.XX ± .XX		TP24939C01	
.XXX ± .XXX		SHT 1 OF 1	
ANGLES ± °		SIZE	
THIRD ANGLE PROJECTION		C	
DRWN BY	DATE	CHK	SCALE
DCS	04-06-05	MBR	3/4