



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FOR MOUNTING
SCREW
(SUPPLIED; QTY 2)

.03 [0.8] MIN. (MATERIAL THICKNESS)



- NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
 2. SUITABLE TO WALL MATERIAL THICKNESSES OF 1/2" TO 1-1/2".

| | |
|--|---|
| DIMENSIONS IN BRACKETS ARE METRIC [mm] | |
| CAD FILENAME/LAYERS G03668DH_DC_GB3668DH/02A | |
| PANDUIT CORP. TINLEY PARK, ILLINOIS | |
| LV-W-1G SINGLE GANG LOW VOLTAGE WALL PLATE | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ±5° | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. |
| DRAWN BY ARHA DATE 09-17-09 CHK'D KLN | MAT'L: PRE-GALVANIZED STEEL SCALE 1:1 DRAWING NO. GB3668DH DWG SIZE A |

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |
|-----|----------|------|-----|-----------------|----------|-----|------|-----|
| O2A | 09/17/09 | ARHA | AKK | INITIAL RELEASE | GB3668DH | O2A | KLN | |