



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	USED WITH CABLE TIES	HOLE SIZE in (mm)	WEIGHT lbs/ 100 pc (g)/
SGMPMWH32	M, I, S, LH, H SG100M, SG150I, SG200S, SG250S, SG300S, SG370S, SG350LH, SG450H	.315 DIA. X 1.41 DP (8 DIA. X 35.8 DP)	0.67 (303)
MPMWH32			

NOTES:

- \* 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2. BAG MAY CONTAIN EXTRA PIECES TO COMPENSATE FOR VARIANCE IN THE PACKAGING PROCESS. PANDUIT ASSURES MINIMUM PIECE COUNT AS STATED ON THE BAG.

TITLE <b>SUPER GRIP MASONRY PUSH MOUNT SGMPMWH32 &amp; MPMWH32</b>		CUSTOMER DRAWING	
ITEM REVISION NAME <b>G03597HC/01</b>		<b>PANDUIT</b>	
DATASET FILE NAME <b>G03597HC_DC_GB0201BA_06/01</b>			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: <b>IMPACT RESISTANT WEATHER RESISTANT NYLON 6/6 COLOR: BLACK</b>	
.x ± 0.1 [2.5]      .xxx ± 0.02 [0.5] .xx ± 0.05 [1.3]      ANGLES ± 5°		DRAWING NUMBER: <b>GB0201BA</b>	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY <b>TMSA</b>	DATE <b>5/23/06</b>	CHK <b>JADE</b>	SCALE <b>FULL</b>
REV	DATE	BY	CHK
6	1/25/2021	RVU	JADE
5	9/04/02	TMSA	
DESCRIPTION		APR	ECN
ADDED NOTE 2.			GAECN05867
COMPLETELY REVISED LAYOUT AND ADDED PART NUMBER SGMPMWH32.			GB0201BA

D10100DA/20