


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
2. GP6 PLUS CONNECTOR ON ONE END AND AN RJ45 MODULAR PLUG WIRED TO EIA/TIA 568A ON THE OTHER END. PATCH CORDS CAN BE USED WITH GP6 PLUS FOUR-PAIR CONNECTING BLOCKS.
3. THE GP6 PLUS PATCH CORD IS POLARIZED TO PREVENT REVERSE INSTALLATION ON THE CONNECTOR BLOCK, INCORPORATES A CABLE JACKET RETENTION FEATURE WHICH MINIMIZES WIRE UNTWISTING, AND HAS AN INTEGRAL STRAIN RELIEF.
4. PATCH CORDS CONSTRUCTED USING UL OR ETL VERIFIED CABLE.
5. MATERIAL:
CONNECTOR: POLYCARBONATE
CABLE: CAT6, 24 AWG STRANDED-TIN/COPPER
JACKET: PVC
JACKET COLOR: WHITE
6. THIS CABLE SHOULD ONLY BE USED IN INTERCONNECT APPLICATION.



PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
GPPC4IG3AY	3 FT.	.91 LB/10 PCS (411 g/10 PCS)
GPPC4IG5AY	5 FT.	1.34 LB/10 PCS (607 g/10 PCS)
GPPC4IG7AY	7 FT.	1.85 LB/10 PCS (838 g/10 PCS)
GPPC4IG9AY	9 FT.	2.30 LB/10 PCS (1041 g/10 PCS)
GPPC4IG14AY	14 FT.	3.42 LB/10 PCS (1550 g/10 PCS)
GPPC4IG20AY	20 FT.	4.79 LB/10 PCS (2172 g/10 PCS)
GPPC4IG1MAY	1 METER	.97 LB/10 PCS (439 g/10 PCS)
GPPC4IG2MAY	2 METERS	1.71 LB/10 PCS (775 g/10 PCS)
GPPC4IG3MAY	3 METERS	2.45 LB/10 PCS (1111 g/10 PCS)
GPPC4IG5MAY	5 METERS	3.93 LB/10 PCS (1783 g/10 PCS)

PART NUMBER		GPPC4IGXAY, GPPC4IGXMAY	
TITLE			
GPS PLUS TO RJ45 EIA/TIA 568A PATCH CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479JU/00	
DATASET FILE NAME		M02479JU_DC257/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ±		.xxx ± .010 [.3]	
.xx ± .03 [.8]		ANGLES ±	
DRAWN BY		SCALE	
NER		NONE	
DATE		SHT 1 OF 1	
3-20-06		A	
CHK		DRAWING NUMBER:	
WJC		02479-257	
SCALE		THIRD ANGLE PROJECTION	
NONE		02479-257	
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5/30/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-257
R	3-20-06	NER	WJC	RMD	RELEASED TO PRODUCTION	02479-257

D10100DA/14