



NO O-RING IS NECESSARY TO OBTAIN IP68 SEAL. CRUSH RIBS ON THE UNDERSIDE OF HEX WILL PROVIDE THE SEAL.

SEALING RANGE: .512 - .708 (13 - 18 MM)
SEAL RATED TO: IP68

MATERIALS	
BODY:	BLACK POLYAMIDE
GROMMET:	NEOPRENE
SPECIFICATIONS:	
TIGHTENING TORQUE:	7.5 Nm
TEMPERATURE:	-20°C - +100°C
APPROVALS:	
US	UL RECOGNIZED
CANADA	C-UL RECOGNIZED

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MENCOM CORPORATION. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MENCOM CORPORATION IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:	DRAWN BY	DCG
DIMENSIONS ARE IN MM	DRAWN DATE	09/11/2018
TOLERANCES:	CHECKED BY	JJH
FRACTIONAL ±1/64	CHECK DATE	09/11/2018
ANGULAR: MACH ±3° BEND ±5°		
ONE PLACE DECIMAL ±.2		
TWO PLACE DECIMAL ±.1		
MATERIAL	COMMENTS:	
FINISH		
DO NOT SCALE DRAWING		

MENCOM CORPORATION		
TITLE:		
PG 21 CABLE GLAND WITH FLEX TOP		
SIZE	DWG. NO.	REV
B	PCG-21-BS	B
SCALE: 3:2	WEIGHT:	SHEET 1 OF 1