

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CMBA75**Y	3.58 LB/100 PCS (1629g/100 PCS)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN [] ARE IN METRIC.
- FOR FREQUENCY RANGE FROM 10-250MHZ, WITH MEASUREMENTS CALCULATED AT 250MHZ, TYPICAL RESULTS ARE INDUCTANCE 9.18nH, CAPACITANCE 1.6pF.
- PART INCLUDES:
 - 1- MODULE BASE
 - 1- 75ohm BNC COUPLER (ASSEMBLED TO MODULE BASE)
 - 1- LOCK WASHER
 - 1- ROUND SPANNER NUT



PART NUMBER		CMBA75**Y	
TITLE		MINI-COM 75 OHM BNC COUPLER	
		CUSTOMER DRAWING	
ITEM REVISION NAME		M02479GW/01	
DATASET FILE NAME		M02479GW_DC181/01A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			
.x ± .xxx ± .010 [.3] .xx ± .03 [.8]			
ANGLES ±		MATERIAL: COUPLER BODY- NICKEL PLATED COUPLER INSULATOR- PLASTIC COUPLER CONTACT- GOLD PLATED MODULE BASE- PLASTIC	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 02479-181	
DRAWN BY	DATE	CHK	SCALE
JSP	4-26-06	MJD	NONE
SHT 1 OF 1		SIZE A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	6/01/17	MDJR	NAGL	AMY	B. REMOVED NOTE 5.	02479-181
1	5/2/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-181
R	4-26-06	JSP	MJD	MJD	RELEASED TO PRODUCTION	02479-181

2

1

D10100DA/14