

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES, UNLESS OTHERWISE SPECIFIED:

STH2 TOOL FOR INSTALLER CONTROLLED TENSIONING AND FLUSH CUT-OFF OF EXCESS CABLE TIE.

ROTATION FOR CUTOFF: 90°



NO MAINTENANCE: NO REPAIR

COLOR: BLACK WITH RED HANDLE.

** CABLE TIE CROSS-SECTION CODE:

- S = STANDARD
- HS = HEAVY STANDARD
- LH = LIGHT HEAVY
- H = HEAVY

PANDUIT TOOL NO.	INSTALLS • THE FOLLOWING CABLE TIE CROSS-SECTIONS **	WEIGHT/PC	
		OZ	GRAMS
STH2	S,HS,LH,H,	2-1/2	71



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
01	12-8-05	JEH	ABJ	REFORMATED NOTES	4176	--	BKA	
00	2-18-93	BAD	MM	RELEASED	3152	--	M ³	

CAD FILENAME/LAYERS: R19334AA_WE19334B01_01

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DWG, STH2

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 1.XI ± .01
 1.XX ± .02
 ANGLES ± .01

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION

SCALE: NONE

DRAWN BY: B.D. MAT'L: _____

DATE: 2-18-93

DRAWING NO.: WE19334B01 DWG SIZE: B