



IPL3/0-3 SHOWN

PART NUMBER	NO. OF PORTS	LENGTH
IPL3/0-3	3	2.63
IPL3/0-4	4	3.41
IPL3/0-5	5	4.19
IPL3/0-6	6	4.97
IPL3/0-8	8	6.53
IPL3/0-10	10	8.09
IPL3/0-14	14	11.21

NOTES:

- CONNECTOR MANUFACTURED FROM 6061-T6 ALUMINUM ALLOY.
- UL LISTED PER UL486A/B SPECIFICATIONS FOR 600V.
- DUAL RATED FOR 90°C COPPER AND/OR ALUMINUM CONDUCTOR.
- COLD TEMPERATURE RATED TO -45°C.
- HIGH DIELECTRIC STRENGTH INSULATION IS ABRASION, CHEMICAL AND UV RESISTANT.

CONTACT NSi FOR SALES @ 800.321.5847

		<b>POLARIS</b> SALES CO. INC
<small>PROPRIETARY AND CONFIDENTIAL</small>		<small>11625 PROSPEROUS DRIVE ODESSA, FL 33556</small>
<small>THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.</small>		<b>TITLE:</b> INSULATED 3/0 CONNECTOR
<small>NAME</small> S.PARRY	<small>DATE</small> 06/2012	<b>DWG. NO.</b> IPL3/0-
<b>MATERIAL:</b> N/A		<b>SCALE:</b> N/A
		<b>SHEET:</b> 1 OF 1