




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	MAXIMUM CABLE DIA. IN (MM)	PANEL DIMENSIONS		WEIGHT	
		THICKNESS IN (MM)	HOLE SIZE IN (MM)	lbs/100 pcs (g)/100 pcs	
PMCC38H25	0.38 (9.6)	0.105 MAX. (2.7)	0.250 (6.4)	0.26 (120)	



NOTES:

1. SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, MATERIAL AND COLOR.
2. PARTIAL SECTION ON FRONT VIEW IS SHOWN FOR CLARITY.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G00239DA_PB_PMCC38H25_03

PANDUIT CORP. TINLEY PARK, ILLINOIS

PMCC38H25
PUSH MOUNT CORD CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY CBJ

MAT'L:

SCALE NONE

DATE 3-13-96

NYLON

DRAWING NO. G00239DA

DWG SIZE A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	O.C.
4	12-17-10	BWG	MJVE	REVISED NOTE 1, MADE MAT'L. NYLON.	G00239DA	4	PBC		