


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
2. CLIP IS DESIGNED TO BE USED TO SUPPORT J HOOK ON WIRE, THREADED AND UNTHREADED ROD, AND 1/8" TO 7/16" THICK FLANGES.
3. HOOK MATERIAL: NYLON 6/6
CLIP MATERIAL: SPRING STEEL
RIVET MATERIAL: ALUMINUM
4. PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 4" DIA. BUNDLE, POSITIONING ONLY.
5. PRODUCT INCORPORATES FEATURES THAT ALLOW USER TO RETAIN CABLE BUNDLES IN J PRO J HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
6. PRODUCT IS UL RATED FOR USE IN AIR HANDLING SPACES AT 4 FT MIN SPACING.

PANDUIT P/N	MOUNTING	WEIGHT (10 PCS)
JP4DW-X20	1/8" - 7/16" FLANGES; #12 - 3/8" DIAM ROD	5.4 LBS (2467 g)

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:	DRAWING NUMBER:	SIZE
0	3/14/16	DFA	CLW	JHAC	INITIAL RELEASE	GAECN03793	JP4DW - JP4 DROP WIRE CUSTOMER DRAWING	NYLON WITH STEEL CLIP	10K016XY_DC	A
							ITEM REVISION NAME: 10K016XY/01 DATASET FILE NAME: 10K016XY_DC/01 UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 ° THIRD ANGLE PROJECTION			
							DRAWN BY: DFA DATE: 3/14/16 CHK: JHAC SCALE: 1:4	SHT 1 OF 1		