



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT (APPROX.)
NK6PPG12WY	1.25 lb (567 g)

- NOTES:
- MATERIAL:
 PANEL HOUSING: STEEL/BLACK POWDER COAT
 RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
 PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
 BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
 RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
 - 12 PORT PATCH PANEL WITH TWO 6 POSITION BEZELS ASSEMBLIES, 8 WIRES PER JACK ASSEMBLY.
 - THE PATCH PANEL IS DESIGNED TO SNAP INTO A STANDARD S89D WALL MOUNT BRACKET.
 - DIMENSIONS IN [] ARE IN METRIC.
 - USE 110 STYLE TERMINATION TOOL FOR PUNCH DOWN.
 - RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.



PART NUMBER		NK6PPG12WY	
TITLE			
NETKEY CATEGORY 6 12 PORT DATA PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479M0/00	
DATASET FILE NAME		M02479M0_DC328/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xxx ± .010 [.3]		SEE NOTES	
.xx ± .03 [.8]		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		02479-328	
DRAWN BY	DATE	CHK	SCALE
NER	3-22-06	WJC	NONE
REV	DATE	BY	CHK
1	6/13/14	JSP	REFR
R	3-22-06	NER	WJC
APR	DESCRIPTION		ECN
	A. REVISED DRAWING TITLE BLOCK.		02479-328
	RELEASED TO PRODUCTION		02479-328
SHT 1 OF 1		A	

D10100DA/14

2

1

2

1