


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA11-A THRU PCA11-Z	'A' THRU 'Z'	30	300	1	10	.110" - .130"
PCA11-A-J	'A'-'J' [1 EA.]	30	300	1	10	.110" - .130"
PCA11-K-T	'K'-'T' [1 EA.]	30	300	1	10	.110" - .130"
PCA11-U-Z	'U'-'Z' [1 EA.] '-' [2 EA.] '+' [2 EA.]	30	300	1	10	.110" - .130"
PCA11-0 THRU PCA11-9	'0' THRU '9'	30	300	1	10	.110" - .130"
PCA11-0-9	'0'-'9' [1 EA.]	30	300	1	10	.110" - .130"
PCA11-MIN	'-'	30	300	1	10	.110" - .130"
PCA11-PLS	'+'	30	300	1	10	.110" - .130"

NOTES:

1. COLOR: WHITE WITH BLACK LEGENDS.
2. MILLIMETERS ARE IN [].
3. ONE SIDE PRINTED.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	10/27/15	RVU	SEWH	JHAC	ADD NOTE 3 TO SHOW THAT ONE SIDE PRINTED.	GAECN03212
4	4/22/13	RVU	SEWH	JHAC	CHANGE OLD DRAWING BOARDER TO NEW PANDUIT DRAWING BOARDER.	GAECN02982
3	3/28/11	RVU			ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [1 EA.].	6336
2	8/11/10	RVU			UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.	6079
1	10/6/06	RVU			ADDED TOLERANCE AND REVISED TABLE.	4881
0	9/12/06	RVU			DRAWING RELEASE.	3732

TITLE PCA11-* CLIP-ON WIRE MARKER					
CUSTOMER DRAWING					
ITEM REVISION NAME 100281DB/06			PANDUIT		
DATASET FILE NAME 100281DB_DS_C10351/06F					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					
.x ± .12 [3.05]		.xxx ± .025 [.635]		MATERIAL: WHITE MARKER-ACETAL	
.xx ± .062 [1.57]		ANGLES ±		DRAWING NUMBER: C10351	
DRAWN BY RVU			DATE 10/14/04		CHK JM
SCALE NTS			THIRD ANGLE PROJECTION		
SHT 1 OF 1			SIZE A		

D10100DA/15